


Dynamic Sonic Cleaning Action, up to 40,000 brush strokes/min



The high frequency sonic technology is clinically proven to remove up to 100 percent more plaque bio film in hard-to-reach areas and to whiten teeth up to two times better within one week than a manual toothbrush.

Naturally Whiter Teeth

Daily use of the White mode can help you achieve teeth that are noticeably whiter in just 1 week. Proven to remove coffee, tea, tobacco and red wine stains. The advanced new handle, high-density, diamond-shaped bristles and range of five cleaning modes offer a clinical-level clean that dentists recommend it to their patients.



PULSE

OraSonic Corp.
Tampa, FL

PULSE

APP Guided ToothBrush















PULSE

Pulse Smart Sonic Toothbrush
16 Brush Areas Detect & Wireless Charging



Excellent Features

- | | | | |
|--|---|--|---|
| 
One Button Power & Mode Selection | 
Up to 40,000 Brush Strokes/Min | 
Up to One Month Battery Life | 
Five Brushing Mode |
| 
DuPont Bristle | 
Wireless Charger | 
Smart Timer | 
16 Brush Area Guidance |
| 
Bluetooth 4.0 Connectivity | 
Low Battery Indicator | 
Reminder Bristles Fade for Brush Head Replacement | 
Waterproof IPX7 |

16 Area Brushing Guidance, Sweep Away the Plaque Everywhere

- Bluetooth 4.0 Connectivity
- Brush Area Detecting Technology
- 16 Brushing Area Guidance
- 5 Brush Modes Supported
- Wireless Base Charger
- Wireless Charging Travel Box

Brush Area Detecting Technology

- Tracks where you've brushed, highlights where you haven't
- Start taking better care of your problem areas
- Takes you back to any missed spots for 100% coverage

PULSE Sonic toothbrush is a highly versatile brush and is suitable for a wide range of users due to its five bespoke brush modes. This versatility allows users to tailor their brushing experience to their own needs as well as their dental professional's advice. The brush modes range from:

Five Brushing Modes

Clean

The ultimate in the plaque removal

White

Whitening mode of 2 minutes to remove surface stains, plus an additional 30 seconds to brighten and polish your front teeth.

Polish

Dental polishing, whiten the teeth

Soft

Extra gentle mode for sensitive teeth and gums

Sensitive

Gentle teeth and gum cleaning

